

### **STEP 1, PER FIGURE 1**

SET UP CABLE TRIM MACHINE, SINGLE EDGED RAZOR BLADE & CUT RESISTANT GLOVE.

TRIM JACKET ONLY TO DIMENSION SHOWN.

# **STEP 2, PER FIGURE 2**

SET UP SOLDER TWEEZER, SOFT SOLDER, SOLDER FIXTURE, IONOX SOLUTION, BRUSH AND Q-TIP OR KIMWIPE.

SLIDE CABLE INTO CONNECTOR BODY AS SHOWN, SOFT SOLDER ALL AROUND AS SHOWN. SOLDER APPLIED TO REAR SIDE OF BODY. SEE NOTE 3.

### **STEP 3, PER FIGURE 3**

SET UP FACE TOOL AND POINTING FIXTURE

TRIM DIELECTRIC BACK FLUSH TO BODY BEING CAREFUL NOT TO NICK INNER CONDUCTOR

POINT INNER CONDUCTOR AS SHOWN.

## **STEP 4, PER FIGURE 4**

ASSEMBLE GASKET, LOCK RING AND COUPLING NUT TO BODY

VERIFY THERE IS NO SOLDER ON THIS SURFACE PRIOR TO FINAL ASSEMBLY WHEN SOLDERING FROM INTERFACE

REVISION HISTORY

DESCRIPTION

D

DCN 39867

APPROVED

STW

DATE

06/13

SOLDER TO JACKET 360° SOLDER SHALL NOT EXTEND ONTO OUTSIDE OF BODY



### NOTES:

- CABLE ASSEMBLY INSTRUCTIONS FOR SEMI RIGID AND COMFORMABLE CABLE.
- SOLDER TYPE PER CABLE ASSEMBLY BOM.
- IF CABLE ASSEMBLY DRAWING REQUIRES TO SOLDER FROM THE INTERFACE SIDE, SEE FIGURE 5.

MATERIAL PER BOM FINISH: PER BOM SURFACE AREA: N/A **PROPRIETARY** THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED. SF2902-6001

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL:  $\pm 1/64$  ANGULAR: X°  $\pm 1^{\circ}0'$  X°X'  $\pm 15'$ .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION APPROVED: E.M. SIMULATION: N/A

UNLESS OTHERWISE SPECIFIED SV Microwave, Inc. I) ALL DIMENSIONS ARE AFTER PLATING 1) ALL DIMENSIONS ARE AFTER PLATING.
2) BREAK CORNERS & EDGES .005 F. MAX.
3) CHAM. 1ST & LAST THREADS.
4) SURFACE ROUGHNESS 63 4 MIL-STD-10.
5) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.
6) REMOVE ALL BURRS 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409

BRT 05/21/97 DRAWN: CHECKED: DGG 11/02/77

TITLE: **CABLE ASSEMBLY INSTRUCTIONS** 

300-80-014 B 95077 SCALE: 4:1 SHEET 1 OF

USED ON: